

APSH BRAID-REINFORCED SILICONE HOSE

PLATINUM-CURED



Low volatile grade, platinum-cured silicone hose is produced in AdvantaPure's certified Class 1000 clean room for critical pharmaceutical, biomedical, cosmetic, and food applications. Polyester yarn braiding inside the wall enhances pressure capabilities. APSH has undergone extensive physical, chemical, and biological testing and meets USP Class VI, FDA CFR 177.2600, ISO 10993, European Pharmacopoeia 3.1.9, and 3-A standards.

APSH is not intended for implantation and is not to be used for continuous steam applications.




SILICONE

www.advantapure.com

KEY FEATURES





- Hardness value of 65 Shore A (validatable core: 70A; cover: 60A)
- Extremely flexible
- General temperature range: -100°F (-73.3°C) to 400°F (204.4°C)
- Sterilizable by autoclave, CIP, SIP, and gamma radiation processes
- Low volatile grade suitable for pharmaceutical and biomedical applications
- Core made of NSF 51 listed silicone (National Sanitation Foundation)
- Resists temperature extremes, compression set, chemical attack, ozone, radiation, moisture, and environmental exposure
- Imparts no taste or odor to critical streams
- Stocked in 25 and 50 ft. coils
- Manufactured in a certified HEPA-filtered clean room
- Sealed in clear polybags during the manufacturing process to ensure cleanliness
- Documented lot traceable with identification on bags and boxes
- Documented quality control
- Complete validation package available upon request
- Color tracer braid available for easy identification
- Anti-wick seal option available to prevent liquid absorption at hose ends
- Custom lengths, sizes, special cleaning, and/or packaging available
- Available with Nomex® braid construction – call for details



APSH BRAID-REINFORCED SILICONE HOSE

PLATINUM-CURED



SPECIFICATIONS

Product Number	Nominal I.D.		Wall		O.D.		Working Pressure at 70°F (21.1°C)		Burst Pressure* at 70°F (21.1°C)		Minimum Bend Radius		Weight per Foot / Meter	
	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)	(PSI)	(Bar)	(PSI)	(Bar)	(in.)	(mm)	(lb.)	(kg)
APSH-P-0063	.063	1.59	.105	2.67	.282	7.16	200	13.79	775	53.44	CF	CF	.031	.046
APSH-P-0125	.125	3.18	.120	3.05	.375	9.53	175	12.07	700	48.27	CF	CF	.051	.076
APSH-P-0188	.188	4.76	.130	3.30	.462	11.73	170	11.72	650	44.82	CF	CF	.073	.109
APSH-P-0250	.250	6.35	.125	3.17	.500	12.70	140	9.65	550	37.92	1	25.4	.077	.115
APSH-P-0375	.375	9.53	.125	3.17	.625	15.88	140	9.65	550	37.92	1	25.4	.102	.152
APSH-P-0500	.500	12.70	.187	4.75	.875	22.23	105	7.24	420	28.96	3	76.2	.211	.314
APSH-P-0625	.625	15.88	.170	4.32	.990	25.15	100	6.90	400	27.58	3	76.2	.241	.359
APSH-P-0750	.750	19.05	.175	4.45	1.125	28.58	90	6.21	350	24.13	4	101.6	.287	.427
APSH-P-0875	.875	22.23	.180	4.57	1.260	32.00	65	4.48	250	17.24	5	127.0	.336	.500
APSH-P-1000	1.000	25.40	.190	4.83	1.405	35.69	60	4.14	225	15.51	6	152.4	.401	.597

Sold by standard coil length only; 25 or 50 feet available for all sizes. Add length suffix code to product number when ordering—see the Coil Length Legend at right for length suffix codes. Example: 50 ft. of .250 in. I.D. hose is product number APSH-P-0250L.

Coils are supplied heat-sealed in polybags and bulk packed. Contact your AdvantaPure Sales Representative for other packaging options.

*For every 100°F of temperature over 70°F (up to 400°F), reduce the burst pressure by 10%.

CF = Consult factory

Coil Length Legend:

P = 25 feet

L = 50 feet

NOTE: When products are used as part of an assembly, the pressure ratings of fittings may be less than hose pressure ratings above. Please consult your sales representative.

SILICONE

Purity in Fluid Flow SystemsSM

APSH is part of a complete line of products for the Pharmaceutical, Biomedical, Cosmetic, and Food industries. Items available include . . .



- Platinum-cured silicone tubing and mandrel-wrapped, platinum-cured silicone suction hose
- Stainless steel overbraided PTFE hose; rubber-covered FEP and EPDM hose
- Sanitary fittings and complete hose assemblies including molded silicone ends
- Identification solutions including the Hose Track™ Process Equipment ID & Lifecycle Analysis System
- Silicone injection molding capabilities – manifolds, stoppers, and sealing systems for single use processes

Address: NewAge® Industries AdvantaPure®
145 James Way
Southampton, PA 18966 U.S.A.



DISTRIBUTED BY:

Toll Free Phone: **888-755-4370**
Phone: **215-526-2151**
Toll Free Fax: **888-258-4293**
Fax: **215-526-2167**
Web Site: **www.advantapure.com**
E-mail: **sales@advantapure.com**

©2007 NewAge® Industries, Inc. • AdvantaPure products are produced by NewAge® Industries, Inc. Hose Track™, NewAge® Industries AdvantaPure®, the AdvantaPure logo, NewAge® and the "N" logo are trademarks of NewAge® Industries, Inc. Purity in Fluid Flow SystemsSM is a service mark of NewAge® Industries, Inc. Nomex® reg TM E. I. DuPont de Nemours and Company



WARRANTY: NewAge Industries AdvantaPure products are warranted to be free from defects in material and workmanship. Any product found to carry such defects will be replaced without charge. This warranty is limited only to the replacement of NewAge Industries AdvantaPure products, item for item, which after examination by NewAge Industries AdvantaPure are deemed defective. NewAge Industries AdvantaPure specifically disclaims any other liability. The data supplied is provided as a helpful guideline and is believed to be reliable; however, nothing stated shall constitute a guarantee, recommendation, or warranty for any application.

NOTICE: NewAge Industries, Inc. has been a privately owned corporation since 1954. Neither the corporation nor its principals are affiliated, in any way, with any other group or entity either representing themselves as or being referred to by the term NewAge.